



Southwire™

TOOLS & EQUIPMENT



QWIKtape™ Pull Tape
QWIKrope™ Pulling Rope
QWIKline™ Polyline

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™ TOOLS & EQUIPMENT

QWIKtape™ Pull Tape

Southwire QWIKtape™ pulling line increases pulling and installation efficiency on jobsites. It allows you to thread, measure and pull with a single product.

- Thread & measure conduit, then pull wire with one product
- Printed with accurate, sequential, easy-to-read footage markings
- Provides quick and accurate measurement of conduit runs
- Low coefficient of friction minimizes duct melting
- Easily blown through conduit



SWMT2500-3000S



SWMT1800-3000S



SWMT1250-3000S



SWMT400-4500P



*Actual size

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**



Southwire Conduit Measuring Tape

The 3,000 ft conduit measuring tape has easy-to-read markings in sequential one-foot increments.

- Provides quick and accurate measurement of conduit runs
- Printed with accurate sequential footage markings
- Will not rot or mildew

SWCMT160-3000S

160LB SOUTHWIRE CONDUIT MEASURING TAPE

*Actual size



QWIKline™ Poly Line

Poly line for light duty cable or rope pulling applications.

- Ready-to-use storage container quickly dispenses a tangle-free line
- Line is resistant to rot and mildew
- Use to pull electrical and communication wire



1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™ TOOLS & EQUIPMENT

QWIKrope® Pulling Rope

A innovative, new, high performance pulling rope that is UV resistant, lightweight and ultra low stretch.

- High performance pulling rope made from ultra high molecular weight polyethylene fibers
- 12 Strand, single braided 9/16" pulling rope with a breaking strength of 32,000 lbs.



Southwire Double Braided Pulling Rope

Cable pulling rope designed for high breaking strength with low stretch. The double braid weave provides enhanced strength and increased pulling capability.

- High strength and low stretch
- Resistant to UV rays, chemicals and abrasions
- Factory spliced pulling eye at each end
- Polyester double braid



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**



QWIKtape™ Pull Tape

MODEL #	STOCK #	DESCRIPTION	WIDTH	LENGTH	AVG. BRERAKING STRENGTH	PACKAGE
SWMT400-4500P	645850	QWIKtape™ Pull Tape Pail	1/4"	4,500 Ft.	400 lbs.	Bucket
SWMT1250-3000S	645851	QWIKtape™ Pull Tape Spool	1/2"	3,000 Ft.	1,250 lbs.	Plastic Spool
SWMT1800-3000S	645852	QWIKtape™ Pull Tape Spool	5/8"	3,000 Ft.	1,800 lbs.	Plastic Spool
SWMT2500-3000S	645854	QWIKtape™ Pull Tape Spool	3/4"	3,000 Ft.	2,500 lbs.	Plastic Spool

Southwire Conduit Measuring Tape

MODEL #	STOCK #	DESCRIPTION	WIDTH	LENGTH	AVG. BRERAKING STRENGTH	PACKAGE
SWCMT160-3000S	645849	Conduit Measuring Tape Spool	3/16"	3,000 Ft.	160 lbs.	Metal Flange

QWIKline™ Poly Line

MODEL #	STOCK #	DESCRIPTION	WIDTH	LENGTH	AVG. BRERAKING STRENGTH	PACKAGE
PL6500	582805	Tensile Strength Poly Line	3/16"	6,500 Ft.	210 lbs.	Bucket
PL500	582806	Tensile Strength Poly Line	3/16"	500 Ft.	210 lbs.	Canister



MODEL #	STOCK #	DESCRIPTION	WIDTH	LENGTH	AVG. BRERAKING STRENGTH	TOTAL WEIGHT
SPR183	583874	QWIKrope® 1/8" x 300' 12 Strand UHM-WPE Rope AVG. Break 1,100 lbs.	1/8"	300 Ft.	1,100 lbs.	2.5 lbs.
SPR183	583875	QWIKrope® 1/4" x 300' 12 Strand UHM-WPE Rope AVG. Break 7,500 lbs.	1/4"	300 Ft.	7,500 lbs.	6.5 lbs.
SPR146	585263	QWIKrope® 1/4" x 600' 12 Strand UHM-WPE Rope AVG. Break 7,500 lbs.	1/4"	600 Ft.	7,500 lbs.	11 lbs.
SPR963	583056	QWIKrope® 9/16" x 300' 12 Strand UHM-WPE Rope AVG. Break 32,000 lbs.	9/16"	300 Ft.	32,000 lbs.	26 lbs.
SPR966	583057	QWIKrope® 9/16" x 600' 12 Strand UHM-WPE Rope AVG. Break 32,000 lbs.	9/16"	600 Ft.	32,000 lbs.	52 lbs.
SPR969	583058	QWIKrope® 9/16" x 900' 12 Strand UHM-WPE Rope AVG. Break 32,000 lbs.	9/16"	900 Ft.	32,000 lbs.	77 lbs.
SPR9612	583059	QWIKrope® 9/16" x 1,200' 12 Strand UHM-WPE Rope AVG. Break 32,000 lbs.	9/16"	1,200 Ft.	32,000 lbs.	103 lbs.



MODEL #	STOCK #	DESCRIPTION	WIDTH	LENGTH	AVG. BRERAKING STRENGTH	TOTAL WEIGHT
P-963	568235	9/16" 300 Ft., Double Braided Composite Rope AVG Break. 16,000 lbs.	9/16"	300 Ft.	16,000 lbs.	50 lbs.
P-966	568236	9/16" 600 Ft., Double Braided Composite Rope AVG Break. 16,000 lbs.	9/16"	600 Ft.	16,000 lbs.	75 lbs.
P-583	568237	5/8" 300 Ft., Double Braided Composite Rope AVG Break. 18,000 lbs.	5/8"	300 Ft.	18,000 lbs.	63 lbs.
P-586	568239	5/8" 600 Ft., Double Braided Composite Rope AVG Break. 18,000 lbs.	5/8"	600 Ft.	18,000 lbs.	85 lbs.
P-786	568240	7/8" 600 Ft., Double Braided Composite Rope AVG Break. 32,000 lbs.	7/8"	600 Ft.	32,000 lbs.	240 lbs.
P-789	577913	7/8" 900 Ft., Double Braided Composite Rope AVG Break. 32,000 lbs.	7/8"	900 Ft.	32,000 lbs.	269 lbs.
P-7812	568241	7/8" 1,200 Ft., Double Braided Composite Rope AVG Break. 32,000 lbs.	7/8"	1,200 Ft.	32,000 lbs.	298 lbs.

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**



1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & TMTrademark of Southwire Company, LLC.



Southwire™

TOOLS & EQUIPMENT



GET SOCIAL WITH US:



/SOUTHWIRETOOLS
/SOUTHWIRETOOLSLATINO



@SOUTHWIRETOOLS



@SOUTHWIRETOOLS



SOUTHWIRETOOLS

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.