


SmartRack 12U Server-Depth Wall-Mount Small Rack Enclosure, Hinged Back

MODEL NUMBER: SRW12US33



Wall-mount cabinet secures and organizes 12U of 19-inch rack equipment in network closets, classrooms and other locations with limited floor space. Houses equipment up to 32.5 inches deep, including 1U servers.

Description

The SRW12US33 SmartRack 12U Server-Depth Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 250 lbs (113.4 kgs).

The cabinet swings away from the wall on a sturdy hinge, allowing easy back-door access to equipment and cabling during installation and maintenance. The doors and side panels lock securely to help prevent damage, tampering or theft. The front, top, bottom and removable side panels are vented, which allows air to flow freely and keep equipment cool. The reversible doors can open left or right by rotating the cabinet 180° before mounting. Convenient top and bottom ports allow easy cable routing.

The SRW12US33 comes fully assembled and ready to mount to the wall, or use Tripp Lite's optional SRCASTER rolling caster kit to make it a mobile rack. Square and 12-24 threaded mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails adjust in 7/8-inch increments to accommodate equipment up to 32.5 inches deep, such as 1U servers, UPS systems, battery packs, network switches and patch panels.

Features

Saves Valuable Workspace

- Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way
- Houses deep EIA-standard 19 in. rack equipment in 12U of space

Highlights

- Maximum load capacity of 250 lbs (113.4 kgs)
- Swings away from wall on hinge for easy back-door access
- Locking steel cabinet vented at sides, front, top and bottom
- Flow-through ventilation keeps equipment cool
- Secures 12U of 19 in. rack equipment up to 32.5 in. deep

Package Includes

- SRW12US33 SmartRack 12U Server-Depth Wall-Mount Rack Enclosure Cabinet
- (36) M6 screws
- (36) M6 cage nuts
- (36) M6 washers
- (36) 12-24 screws
- (2) Keys
- Owner's manual



- Maximum load capacity of 250 lbs (113.4 kgs)

Hinged Cabinet for Convenient Access

- Swings away from the wall to allow easy back-door access to equipment and cabling during installation and maintenance
- Rotate cabinet 180° before mounting to open reversible doors left or right

Keeps Important Equipment Secure

- Side panels and doors lock securely to help prevent damage, tampering or theft
- Vented panels allow generous airflow that keeps equipment cool
- Convenient ports with removable covers allow cable routing through top and bottom

Easy Enclosure and Equipment Installation

- Ships fully assembled for quick installation
- Mounts to wall or rolls on floor with Tripp Lite's optional SRCASTER caster kit
- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Vertical mounting rails adjust in 7/8 in. increments to accommodate equipment up to 32.5 in. deep, such as 1U servers, UPS systems, battery packs, network switches and patch panels
- Rails support square-hole or 12-24 threaded-hole mounting
- Rack spaces numbered for easy reference

Meets Payment Card Industry Standards

- Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

OVERVIEW	
UPC Code	037332156044
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Enclosure
PHYSICAL	
Color	Black
Factory Preset Rack Depth (in.)	25.99
Factory Preset Rack Depth (cm)	66.0
Factory Preset Rack Depth (mm)	660
Maximum Device Depth (cm)	82.55
Maximum Device Depth (in.)	32.5
Maximum Device Depth (mm)	826
Minimum Device Depth (cm)	7.62



Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Rack Height	12U
Shipping Dimensions (hwd / cm)	76.71 x 66.29 x 91.59
Shipping Dimensions (hwd / in.)	30.20 x 26.10 x 36.06
Shipping Weight (kg)	50.17
Shipping Weight (lbs.)	110.60
Unit Dimensions (hwd / cm)	63.5 x 60 x 85.09
Unit Dimensions (hwd / in.)	25 x 23.63 x 33.5
Unit Weight (kg)	45.36
Unit Weight (lbs.)	100
Weight Capacity - Stationary (kg)	113
Weight Capacity - Stationary (lbs.)	250
Rack Depth	Mid
Number of Vertical Mounting Rails	4
FEATURES & SPECIFICATIONS	
Grounding Lug	Front and Back door frames
STANDARDS & COMPLIANCE	
Approvals	EIA-310-D, IEC 60297-3-100, IP20 Protection Rating, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>