



# PASS & SEYMOUR® Stainless Steel One & Two Gang Wall Plates

SS1, SS2, SS8, SS82, SS26, SS262, SS13, SS23, SS7, SS72, SS720

## Our most corrosion-resistant metal wall plates.


These brushed-finish wall plates are made with .032" Type 302/304 stainless steel. This alloy is nonmagnetic and contains 18 percent chromium and 8 percent nickel for superior corrosion resistance. As a result, these plates will endure in corrosive atmospheres — and withstand abuse in any commercial application.



### FEATURES & BENEFITS

Constructed of .032 inch thick Type 302/304 brushed stainless steel.

Aesthetically pleasing contour design.



Packaged in protective film, with finish-matching screws.

SS262, SS13

### FIELD USES/VERTICAL MARKETS












- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

# PASS & SEYMOUR®

## Stainless Steel

### One & Two Gang Wall Plates

#### Ordering Information

Description	Catalog Number	Description	Catalog Number
<b>Stainless Steel Toggle Switch Openings</b>			
One Gang 	SS1	Two Gang 	SS2
<b>Stainless Steel Duplex Receptacle Openings</b>			
One Gang 	SS8	Two Gang 	SS82
<b>Stainless Steel Decorator Openings</b>			
One Gang 	SS26	Two Gang 	SS262
<b>Stainless Steel Blank Plates — Box Mounted</b>			
One Gang 	SS13	Two Gang 	SS23
<b>Stainless Steel Single Receptacle Openings</b>			
One Gang 	SS7	Two Gang 	SS72
<b>Stainless Steel Power Outlet Receptacle Opening</b>			
One Gang 	SS720		

Custom painted wall plates are available in the following colors. Add suffix to the part number.

COLOR	SUFFIX
Orange	ORG
Green	GRN
Gray	GRY
Yellow	YFI
Glossy Black	GBK
Brown	BRO
White	WHT
Primer	PRI
Red	RED
Pink	PNK
Flat Black	FBK
Ivory	IVY
Light Almond	LTA
Blue	MBL

All paint finishes are gloss, except primer and flat black. Only available on stainless steel and aluminum plate material.

For more information on these and other P&S products refer to our Product Guide or visit our web site.

# PASS & SEYMOUR Stainless Steel One & Two Gang Wall Plates



## Technical Specifications

### 3rd Party Compliance

UL Listed, Standard UL514, Cover Plates for Flush Mounted Wiring Devices.  
CSA Certified.

### Performance

Environmental Corrosion-Resistant

### Materials


Plate Material	.032" 302/304 Stainless Steel
Plate Finish	Brushed
Screws	302/304 Stainless Steel

### Warranty


1 Year

### Country of Origin

USA




Dimensions for  
One Gang



Dimensions for  
Two Gang

## COMPLEMENTARY DEVICES & ACCESSORIES



### TURNLOK® LOCKING DEVICES

- Heavy-Duty Receptacles
- Heavy-Duty Flanged Inlets & Outlets



### GROUND CONTINUITY MONITORING (GCM)

- Extra-Hard Use Straight Blade
- Heavy-Duty Turnlok®



### STRAIGHT BLADE PLUGS & CONNECTORS

- Extra-Hard Use
- Heavy-Duty MaxGrip® M<sup>3</sup>



### SPD & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok® Isolated Ground
- Heavy-Duty Isolated Ground SPD
- Heavy-Duty SPD
- Construction Grade SPD



### IEC 309 INDUSTRIAL PRODUCTS

- Fusible & Non-Fusible Mechanical Interlocks
- Fusible & Non-Fusible Safety Switches
- Pin & Sleeve Devices

## ALSO AVAILABLE...

- Lighting Controls
- USB Charging Devices
- Hospital Grade Devices
- PlugTail Devices
- GFCIs
- SPD Isolated Ground Devices
- Ground Continuity Monitoring Devices
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips



### Electrical Wiring Systems

P.O. Box 4822  
Syracuse, NY 13221-4822  
Phone: 1.800.776.4035  
[www.legrand.us/passandseymour](http://www.legrand.us/passandseymour)  
570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
Phone: 905.738.9195  
[www.legrand.ca](http://www.legrand.ca)





# PASS & SEYMOUR® Stainless Steel One & Two Gang Wall Plates

SS1, SS2, SS8, SS82, SS26, SS262, SS13, SS23, SS7, SS72, SS720

## Our most corrosion-resistant metal wall plates.


These brushed-finish wall plates are made with .032" Type 302/304 stainless steel. This alloy is nonmagnetic and contains 18 percent chromium and 8 percent nickel for superior corrosion resistance. As a result, these plates will endure in corrosive atmospheres — and withstand abuse in any commercial application.



### FEATURES & BENEFITS

Constructed of .032 inch thick Type 302/304 brushed stainless steel.

Aesthetically pleasing contour design.



Packaged in protective film, with finish-matching screws.

SS262, SS13

### FIELD USES/VERTICAL MARKETS












- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

# PASS & SEYMOUR®

## Stainless Steel

### One & Two Gang Wall Plates

#### Ordering Information

Description	Catalog Number	Description	Catalog Number
<b>Stainless Steel Toggle Switch Openings</b>			
One Gang 	SS1	Two Gang 	SS2
<b>Stainless Steel Duplex Receptacle Openings</b>			
One Gang 	SS8	Two Gang 	SS82
<b>Stainless Steel Decorator Openings</b>			
One Gang 	SS26	Two Gang 	SS262
<b>Stainless Steel Blank Plates — Box Mounted</b>			
One Gang 	SS13	Two Gang 	SS23
<b>Stainless Steel Single Receptacle Openings</b>			
One Gang 	SS7	Two Gang 	SS72
<b>Stainless Steel Power Outlet Receptacle Opening</b>			
One Gang 	SS720		

Custom painted wall plates are available in the following colors. Add suffix to the part number.

COLOR	SUFFIX
Orange	ORG
Green	GRN
Gray	GRY
Yellow	YFI
Glossy Black	GBK
Brown	BRO
White	WHT
Primer	PRI
Red	RED
Pink	PNK
Flat Black	FBK
Ivory	IVY
Light Almond	LTA
Blue	MBL

All paint finishes are gloss, except primer and flat black. Only available on stainless steel and aluminum plate material.

For more information on these and other P&S products refer to our Product Guide or visit our web site.

# PASS & SEYMOUR Stainless Steel One & Two Gang Wall Plates



## Technical Specifications

### 3rd Party Compliance

UL Listed, Standard UL514, Cover Plates for Flush Mounted Wiring Devices.  
CSA Certified.

### Performance

Environmental Corrosion-Resistant

### Materials


Plate Material	.032" 302/304 Stainless Steel
Plate Finish	Brushed
Screws	302/304 Stainless Steel

### Warranty


1 Year

### Country of Origin

USA




Dimensions for  
One Gang



Dimensions for  
Two Gang

## COMPLEMENTARY DEVICES & ACCESSORIES



### TURNLOK® LOCKING DEVICES

- Heavy-Duty Receptacles
- Heavy-Duty Flanged Inlets & Outlets



### GROUND CONTINUITY MONITORING (GCM)

- Extra-Hard Use Straight Blade
- Heavy-Duty Turnlok®



### STRAIGHT BLADE PLUGS & CONNECTORS

- Extra-Hard Use
- Heavy-Duty MaxGrip® M<sup>3</sup>



### SPD & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok® Isolated Ground
- Heavy-Duty Isolated Ground SPD
- Heavy-Duty SPD
- Construction Grade SPD



### IEC 309 INDUSTRIAL PRODUCTS

- Fusible & Non-Fusible Mechanical Interlocks
- Fusible & Non-Fusible Safety Switches
- Pin & Sleeve Devices

## ALSO AVAILABLE...

- Lighting Controls
- USB Charging Devices
- Hospital Grade Devices
- PlugTail Devices
- GFCIs
- SPD Isolated Ground Devices
- Ground Continuity Monitoring Devices
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips



### Electrical Wiring Systems

P.O. Box 4822  
Syracuse, NY 13221-4822  
Phone: 1.800.776.4035  
[www.legrand.us/passandseymour](http://www.legrand.us/passandseymour)  
570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
Phone: 905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

