



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SSTG2 3/4" SS Myers Hub *Crouse-Hinds*

Catalog Number	SSTG2
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Myers Ground Hub, Stainless Steel, 3/4"
Weight per unit	0.4200 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Threaded
dimensions	3.2100 IN X 2.0300 IN X 1.2000 IN
Material	316 Stainless Steel

### Material, Color, and Finish

Finish	Natural
--------	---------

### Dimensions and Weight

Size	3/4 in
------	--------

### Descriptions

Construction	Stainless Steel
Description	3/4" SS MYERS HUB
extra long description	MYERS SSTG 2 CH MYERS 3/4 STAINLESS
Features	Crouse-Hinds series Myers hubs are used in the termination of electrical circuits through wall of an enclosure. They are designed for use indoors or outdoors with rigid conduit and IMC, and they are ideal for pharmaceutical, chemical and food processing, pulp/paper, nuclear, solar and commercial construction applications.
Long Description	Eaton Crouse-Hinds series Myers ground hub, Stainless steel, 3/4"
Product Type	CH Myers 3/4 Stainless Steel Hub
Special Features	Vibration Proof, Posi-Lok Insulated Throat, Weight 30 Lb per 100

### Manufacturer Information

Brand	Eaton
GTIN	00784731100313
Manufacturers Part Number	SSTG 2
UPC	784731100313

### Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Ground Hub



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.42

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure standard	NEMA 2/3/3R/4/4X/12 UL 514B, CUL, CSA C22.2