

Eaton STL61A433CH

Catalog Number: STL61A433CH

Eaton meter socket, Transformer rated socket, 20A, Under, Solid top, Six-jaw, Pre-wired test switch, 600 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton meter socket	STL61A433CH
UPC	Product Length/Depth
786685703411	5.3 in
Product Height	Product Width
21.8 in	12.6 in
Product Weight	Warranty
25 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed	Austin Energy Approved, tranformer rated

Type

Transformer rated socket

Amperage Rating

20A

Feed type

Bottom

Number of jaws

Six-jaw

Voltage rating

600 V

Accessories

Pre-wired test switch

Number of sockets

1

Drawings

[Dimensional Drawing - SKT/SW 20A 6T FW ST](#)

Specifications and datasheets

[Eaton Specification Sheet - STL61A433CH](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia