

# STR-4C-40K-U



<b>Description</b>	LED Strip 4 ft. DLC V4.0 Premium 46W-6026LM 0-10V Dimmable 4000K 120-277V
<b>Ordering Code</b>	09536
<b>UNSPSC Code</b>	39112102

## Specifications

<b>Voltage Rating</b>	120~277
<b>Voltage Type</b>	AC
<b>Watts</b>	46
<b>Lumens per Watt</b>	131
<b>Lumens</b>	6026
<b>CT deg K</b>	4000
<b>CRI</b>	80+
<b>Rated Life</b>	50000
<b>Ambient Operating Temp Range</b>	-20° C (-4° F) to 50° C (122° F)

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975  
Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335



# STR-4C-40K-U



**Description** LED Strip 4 ft. DLC V4.0 Premium 46W-6026LM 0-10V Dimmable 4000K 120-277V

**Ordering Code** 09536

**UNSPSC Code** 39112102

## Specifications

<b>Voltage Rating</b>	120~277
<b>Voltage Type</b>	AC
<b>Watts</b>	46
<b>Lumens per Watt</b>	131
<b>Lumens</b>	6026
<b>CT deg K</b>	4000
<b>CRI</b>	80+
<b>Rated Life</b>	50000
<b>Ambient Operating Temp Range</b>	-20° C (-4° F) to 50° C (122° F)

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335