



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

SU1500RTXLCDU Tripplete Ups System Su1500rtxlcd

Eaton Power Quality

Catalog Number	SU1500RTXLCDU
Manufacturer	Eaton Power Quality
Description	Tripp Lite Series Smartonline 1500VA 1350W 120V Double-Conversion Ups - 8 Outlets, Extended Run, Network Card Option, LCD, Usb, DB9, 2U Rack/Tower
Weight per unit	42.6 (lbs/each)
Product Category	20240322131518

Features

amperage rating	1500
Battery Type	Valve Regulated Lead Acid (VRLA)
charge time	3 hours recharge to 90%
dimensions	17.7200 IN X 17.3300 IN X 3.4100 IN
Input Voltage	100V AC;110V AC;120V AC
Interface Type	(1) Contact closure;(1) RS-232;(1) Slot for SNMP/Web interface;(1) USB
media	Yes
nominal voltage	100V AC;110V AC;120V AC
Number of Outlets	(8) 5-15R
Outlet	NEMA 5-15P
Phase	1
Plug Type	5-15P
Voltage Rating	100V AC;110V AC;120V AC V
Wattage	1350 W

Dimensions and Weight

Depth	17.720
Height	3.41
Width	17.33



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	TRIPLOTE UPS SYSTEM SU1500RTLCDU
extra long description	TRIPP SU1500RTLCD2U SU1500RTLCD2U
Features	The Tripp Lite series SmartOnline UPS lineup provides network-grade power protection and battery backup for critical equipment. Available in rack/tower, 1U rack, and tower form factors, this online double-conversion UPS delivers the highest level of power protection for networking, medical, automation, and light industrial equipment. Pure sine wave AC output and optional extended battery modules (where applicable) ensure the SmartOnline UPS provides advanced battery backup to keep sensitive equipment runni
Long Description	Tripp Lite series SmartOnline 1500VA 1350W 120V Double-Conversion UPS - 8 Outlets, Extended Run, Network Card Option, LCD, USB, DB9, 2U Rack/Tower
Product Type	Su1500rtxlcd2u
Special Features	1.5kVA 1.35kW 120V Battery Backup Protects Equipment against Damage, Downtime and Data LossThis on-line double-conversion UPS system maintains perfect output by converting AC input to DC, then reconverting UPS output to fully regulated sine wave AC. Constant on-line operation completely isolates sensitive equipment from every power problem on the AC line. The SmartOnline® SU1500RTLCD2U double-conversion UPS provides the highest level of power protection and battery backup for education, healthcare, milita

Manufacturer Information

Brand	Eaton Power Quality
Manufacturers Part Number	SU1500RTLCD2U

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	UPS

Packaging

Carton	1
Weight	42.55
Weight Per each	42.55



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Critical PowerCommercial / Institutional Buildings / Structures - Power Distribution and Controls
Operating Temperature standard	32° to 104°F (0° to 40°C) UL 1778 ,CSA certified ,cULus Listed,RoHS ,FCC Class A ,FCC Compliant ,CE Marked
Temperature Rating	32° to 104°F (0° to 40°C)