



## T20P11S25AEE 25KVA Vent'D XFMR 1PH 150C Rise

*Eaton Corp*

|                  |  |
|------------------|--|
| Catalog Number   | T20P11S25AEE   |
| Manufacturer     | Eaton Corp   |
| Description      | Purge-Dry Type Distribution Vent. Transformer, DS-3, Single-Phase, Prim. Voltage: 240 X 480V, Taps: 1 At +5% Fcan, 2 At -5% FCBN X 2 At +2.5% Fcan, 4 At -2.5% FCBN, Sec. Voltage: 120/240V, 150°C, 25 Kva, Al Windings, FR842, 3XA, 60 HZ, Nema |
| Weight per unit  | N/A  |
| Product Category | 20140228075503   |

### Features

|                   |            |
|-------------------|------------|
| design            | DS-3       |
| Primary Voltage   | 240 x 480V |
| Secondary Voltage | 120/240V   |

### Dimensions and Weight

|        |          |
|--------|----------|
| Height | 33.75 IN |
| Length | 17.4 IN  |
| Width  | 22.45 IN |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 25KVA VENT'D XFMR 1PH 150C RISE  |
| extra long description | ETN T20P11S25AEE Eaton General purp  |
| Long Description       | PURGE-Dry type distribution vent. transformer, DS-3, Single-phase, Prim. voltage: 240 x 480V, Taps: 1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN, Sec. voltage: 120/240V, 150°C, 25 kVA, Al windings, FR842, 3XA, 60 Hz, NEMA |
| Product Type           | Eaton General Purpose Ventilated Transformer   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786680109560 |
| Manufacturers Part Number | T20P11S25AEE   |
| UPC                       | 786680109560   |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | 1 PHASE TRANSFORMERS                          |
| Type                 | Dry type distribution, ventilated transformer |

### Packaging

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 0 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4712 E Highland Dr  
72401-0000, AR Jonesboro  
Phone: 870-604-1924  
Fax: 870-497-2677

## Uses, Certifications, and Standards

|                    |                    |
|--------------------|--------------------|
| Application        | Power Distribution |
| Enclosure          | NEMA 2             |
| Frequency Rating   | 60 Hz              |
| standard           | UL Listed          |
| Temperature Rating | 150°C              |