



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T20P11S25AEE 25KVA Vent'D XFMR 1PH 150C Rise *Eaton Corp*

Catalog Number	T20P11S25AEE
Manufacturer	Eaton Corp
Description	Purge-Dry Type Distribution Vent. Transformer, DS-3, Single-Phase, Prim. Voltage: 240 X 480V, Taps: 1 At +5% Fcan, 2 At -5% FCBN X 2 At +2.5% Fcan, 4 At -2.5% FCBN, Sec. Voltage: 120/240V, 150°C, 25 Kva, Al Windings, FR842, 3XA, 60 HZ, Nema
Weight per unit	N/A
Product Category	20140228075503

Features

design	DS-3
Primary Voltage	240 x 480V
Secondary Voltage	120/240V

Dimensions and Weight

Height	33.75 IN
Length	17.4 IN
Width	22.45 IN

Descriptions

Description	25KVA VENT'D XFMR 1PH 150C RISE
extra long description	ETN T20P11S25AEE Eaton General purp
Long Description	PURGE-Dry type distribution vent. transformer, DS-3, Single-phase, Prim. voltage: 240 x 480V, Taps: 1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN, Sec. voltage: 120/240V, 150°C, 25 kVA, Al windings, FR842, 3XA, 60 Hz, NEMA
Product Type	Eaton General Purpose Ventilated Transformer

Manufacturer Information

Brand	Eaton
GTIN	00786680109560
Manufacturers Part Number	T20P11S25AEE
UPC	786680109560

Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Dry type distribution, ventilated transformer

Packaging

Carton	1
Weight Per each	0



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Power Distribution
Enclosure	NEMA 2
Frequency Rating	60 Hz
standard	UL Listed
Temperature Rating	150°C