



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T279744S 5KVA 1PH Transformer

Acme Electric

Catalog Number	T279744S
Manufacturer	Acme Electric
Description	Low Voltage Distribution Transformer - Single Phase, 120/208/240/277 - 120/240V, 5kva
Weight per unit	75.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

Features

pallet quantity	24
Primary Voltage	120/208/240/277
product category	Dry Type Distribution Transformer
Secondary Voltage	120/240

Dimensions and Weight

Height	14.38
Length	7.13
Width	10.31

Descriptions

Construction	ENCAPSULATED
Description	5KVA 1PH TRANSFORMER
extra long description	ACME T279744S TFMR 1PH 5.0KVA 120/2
Long Description	Low Voltage Distribution Transformer - Single Phase, 120/208/240/277 - 120/240V, 5kVA
Product Type	Dry Type Distribution Transformer
Special Features	Encapsulated core and coil; Shielded for cleaner power; Encapsulated and completely enclosed design electrical grade silica and resin compounds completely enclose the core and coil to seal out all moisture and air, UL type 3R enclosure for indoor or outdoor service, encapsulation eliminates corrosion and insulation deterioration; Quiet operation with sound levels well below NEMA standards; 10-year limited warranty

Manufacturer Information

Brand	ACME ELECTRIC
GTIN	00047503102084
Manufacturers Part Number	T279744S
UPC	047503102084

Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Distribution Transformer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	75

Uses, Certifications, and Standards

Enclosure	NEMA 3R Steel
Mounting standard	WALL UL 506, UL File Number E79947V1, UL Control Number 50B8, UL Insulation Number X3221, CSA Certified, OSHA Compliant, ANSI, IEEE
Temperature Rating	115 DEG C Rise