



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TC1R 4" Incandescent Non-Ic Ra

Lithonia Lighting - Acuity

Catalog Number	TC1R
Manufacturer	Lithonia Lighting - Acuity
Description	Incandescent Airtight Housing, Round, 75 W, 120 V, Galvanized, Steel Fixture Material, Aluminum Housing Material, Non Dimmable, 4 In Aperture Size, 1.57 LB
Weight per unit	1.6 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

dimensions	4.75 x 4.75 x 5.25
Lamp Type	Incandescent
Maximum Operating Temperature	25
Power Source	Hardwired
Shape	Round
Warranty	5

Dimensions and Weight

Height	5.25
Length	11.5
Width	4.75

Descriptions

Construction	Remodel
Description	4" INCANDESCENT NON-IC RA
extra long description	LITH TC1R 4IN Incandescent Remodel

Manufacturer Information

Brand	JUNO
GTIN	00661209017987
UPC	661209017987

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	Housing

Packaging

Carton	1
Package	12
Weight Per each	1.57



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

environmental conditions	Indoor
Mounting	Recessed
standard	CSA,UL