



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TC200X200AL Four-Way Mounting Base, Natural Nylon 6.6 For Temp

Abb Installation Products, Inc

| | |
|------------------|--|
| Catalog Number | TC200X200AL |
| Manufacturer | Abb Installation Products, Inc |
| Description | Four-Way Mounting Base, Natural Nylon 6.6 For Temperatures Up to 65 Degrees Celsius (149 F), Length Of 50.8MM (2.0 Inches), Width Of 50.8MM (2.0 Inches), Height Of 7.4MM (0.290 Inches), Self-Adhesive/Screw Mounting Method, #8 Screw, Mounting Hole Size Of 4.3MM (0.169 Inches), 50 Pack |
| Weight per unit | 1.3 (lbs/each) |
| Product Category | Cable Ties & Wraps |

Features

| | |
|----------|---------------------|
| Material | Nylon/Polyamide 6.6 |
|----------|---------------------|

Material, Color, and Finish

| | |
|-------|---------|
| Color | Natural |
|-------|---------|

Descriptions

| | |
|------------------------|--|
| Description | FOUR-WAY MOUNTING BASE, NATURAL NYLON 6.6 FOR TEMP |
| extra long description | ABB TC200X200A-L 4WAY MTG BASE 2X2I |
| Long Description | Four-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 50.8mm (2.0 Inches), Width of 50.8mm (2.0 Inches), Height of 7.4mm (0.290 Inches), Self-Adhesive/Screw Mounting Method, #8 Screw, Mounting Hole Size of 4.3mm (0.169 Inches), 50 Pack |
| Product Type | 4WAY MTG Base 2X2IN Nat Ny SCR/Adh |
| Special Features | Eliminates errors in premounting the base with respect to its orientation to wire bundle direction |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ty-Rap |
| GTIN | 00786210492971 |
| Manufacturers Part Number | TC200X200A-L |
| UPC | 786210492971 |

Taxonomies, Classifications, and Categories

| | |
|------|---------------|
| Type | MOUNTING BASE |
|------|---------------|

Packaging

| | |
|-----------------|------|
| Carton | 50 |
| Weight Per each | 1.25 |

Uses, Certifications, and Standards

| | |
|-----------------------|----------------|
| Mounting | Adhesive/Screw |
| Operating Temperature | -40 to +185 F |