




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TC342A Ty-Rap MTG Base

Abb Installation Products, Inc

| | |
|------------------|--|
| Catalog Number | TC342A |
| Manufacturer | Abb Installation Products, Inc |
| Description | Two-Way Mounting Base, Natural Nylon 6.6 For Temperatures Up to 65 Degrees Celsius (149 F), Length Of 28.6MM (1.13 Inches), Width Of 28.6MM (1.13 Inches), Height Of 6.4MM (0.25 Inches), Self-Adhesive Mounting Method, Bulk Pack |
| Weight per unit | 0.0080 (lbs/each) |
| Product Category | Cable Ties & Wraps |

Features

| | |
|----------|---------------------|
| Material | Nylon/Polyamide 6.6 |
|----------|---------------------|

Material, Color, and Finish

| | |
|-------|---------|
| Color | Natural |
|-------|---------|

Descriptions

| | |
|------------------------|--|
| Description | TY-RAP MTG BASE |
| extra long description | ABB TC342A 2WAY ADH MTG BASE 1.1X1. |
| Long Description | Two-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 6.4mm (0.25 Inches), Self-Adhesive Mounting Method, Bulk Pack |
| Product Type | 2WAY Adh MTG Base 1.1X1.1IN Nat Nyl |
| Special Features | One-piece molding - no lost parts |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ty-Rap |
| GTIN | 00786210823133 |
| Manufacturers Part Number | TC342A |
| UPC | 786210823133 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps |
| Type | MOUNTING BASE |

Packaging

| | |
|-----------------|-------|
| Carton | 1000 |
| Package | 5000 |
| Weight Per each | 0.008 |

Uses, Certifications, and Standards

| | |
|-----------------------|---------------|
| Mounting | Self-Adhesive |
| Operating Temperature | up to 149 F |