



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TC44 Low Voltage Can Housing

Lithonia Lighting - Acuity

Catalog Number	TC44
Manufacturer	Lithonia Lighting - Acuity
Description	The 4-Inch Round Non-Ic, Low Voltage Housing Is Designed to Be Installed In Non-Insulated Areas or Where Insulation Is Spaced At Least 3-Inches From The Housing and Typically Used In New Construction.
Weight per unit	5.0 (lbs/each)
Product Category	Halogen & Quartz Recessed Arch

Features

Hardware	Yes
Lamp Type	Incandescent
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Round
Voltage Rating	012

Material, Color, and Finish

Color	Unfinished
-------	------------

Dimensions and Weight

Height	9
Length	14
Width	14

Descriptions

Construction	New Construction
Description	LOW VOLTAGE CAN HOUSING
extra long description	LITH TC44 4IN Low Voltage New Const
Long Description	The 4-inch round non-IC, low voltage housing is designed to be installed in non-insulated areas or where insulation is spaced at least 3-inches from the housing and typically used in new construction.
Product Type	Housing

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00661209002334
Manufacturers Part Number	TC44
UPC	661209002334



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

aperture size 4 in

Packaging

Carton 1

Weight 5

Weight Per each 5

Uses, Certifications, and Standards

Application Residential

environmental conditions Indoor

Mounting Recessed

standard CSA,UL