

# Specifications

## Eaton TCF100

Eaton Bussmann Series Class CF fuse, TCF, time-delay, dual-element current limiting cube fuse, 100 A, indicating fuse, interrupting rating of 100 kA at 300 Vdc and 300 kA at 600 Vac



### General specifications

PRODUCT NAME	Eaton Bussmann series TCF fuse
CATALOG NUMBER	TCF100
UPC	051712618182
EAN	5027590244091
PRODUCT LENGTH/DEPTH	3.01 in
PRODUCT HEIGHT	2.125 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.284 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked <a href="#">RoHS Compliant</a>
CERTIFICATIONS	UL Listed CSA Certified

Electrical rating	
AMPERAGE RATING	100 A
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
INTERRUPT RATING	100 kAIC at 300 Vdc 300 kAIC at 600 Vac
RESPONSE TIME	10 sec at 500%
VOLTAGE RATING	600 Vac, 300 Vdc

General information	
CLASS	Class CF
CONNECTION	Blade end
FUSE INDICATOR	With Indicator
MOUNTING METHOD	Chassis 35 mm DIN rail
SPECIAL FEATURES	Finger safe
USED WITH	TCFH100N, CCP2-3-100CF

Physical details	
COLOR	Black
FUSE TYPE	Class CF Time delay
MATERIAL	Glass filled PES
NUMBER OF ELEMENTS	Dual
PACKAGING TYPE	Standard

Resources	
CATALOGS	<a href="#">Low Voltage Branch Circuit Fuse Chapter</a> <a href="#">Bussmann Full Line Catalog</a>
COMPLIANCE INFORMATION	<a href="#">RoHS Search Tool</a>
MULTIMEDIA	<a href="#">The Power of Space</a> <a href="#">Bussmann series Fuseology</a>
TECHNICAL DATA SHEETS	<a href="#">Bussmann series UL Class CF CUBEFuse data sheet no. 9000</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:

# Specifications

## Eaton TCF100

Eaton Bussmann Series Class CF fuse, TCF, time-delay, dual-element current limiting cube fuse, 100 A, indicating fuse, interrupting rating of 100 kA at 300 Vdc and 300 kA at 600 Vac



### General specifications

PRODUCT NAME	Eaton Bussmann series TCF fuse
CATALOG NUMBER	TCF100
UPC	051712618182
EAN	5027590244091
PRODUCT LENGTH/DEPTH	3.01 in
PRODUCT HEIGHT	2.125 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.284 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked <a href="#">RoHS Compliant</a>
CERTIFICATIONS	UL Listed CSA Certified

Electrical rating	
AMPERAGE RATING	100 A
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
INTERRUPT RATING	100 kAIC at 300 Vdc 300 kAIC at 600 Vac
RESPONSE TIME	10 sec at 500%
VOLTAGE RATING	600 Vac, 300 Vdc

General information	
CLASS	Class CF
CONNECTION	Blade end
FUSE INDICATOR	With Indicator
MOUNTING METHOD	Chassis 35 mm DIN rail
SPECIAL FEATURES	Finger safe
USED WITH	TCFH100N, CCP2-3-100CF

Physical details	
COLOR	Black
FUSE TYPE	Class CF Time delay
MATERIAL	Glass filled PES
NUMBER OF ELEMENTS	Dual
PACKAGING TYPE	Standard

Resources	
CATALOGS	<a href="#">Low Voltage Branch Circuit Fuse Chapter</a> <a href="#">Bussmann Full Line Catalog</a>
COMPLIANCE INFORMATION	<a href="#">RoHS Search Tool</a>
MULTIMEDIA	<a href="#">The Power of Space</a> <a href="#">Bussmann series Fuseology</a>
TECHNICAL DATA SHEETS	<a href="#">Bussmann series UL Class CF CUBEFuse data sheet no. 9000</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE: