


Eaton TCF30

Catalog Number: TCF30

Eaton Bussmann series TCF fuse, 30 A, 60 Hz, 50 Hz, Dual, Class CF, Black, With indicator, Blade end, Class CF, Time delay, 100 kAIC at 300 Vdc, 300 kAIC at 600 V, Glass filled PES, 600 V, 300 Vdc



General specifications

Product Name	Catalog Number
Eaton Bussmann series TCF fuse	TCF30
UPC	Product Length/Depth
051712615037	1.88 in
Product Height	Product Width
1 in	0.75 in
Product Weight	Compliances
0.08 lb	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	

Electrical rating

Amperage Rating

30 A

Frequency rating - max

60 Hz

Frequency rating - min

50 Hz

Interrupt rating

300 kAIC at 600 Vac

100 kAIC at 300 Vdc

Voltage rating

600 Vac, 300 Vdc

Physical details

Color

Black

Fuse type

Class CF

Time delay

Material

Glass filled PES

Number of elements

Dual

General information

Class

Class CF

Connection

Blade end

Fuse indicator

With Indicator

Special features

Finger safe

Used with

TCFH30N, CCP2-3-30CF

Resources

Catalogs

[Low Voltage Branch Circuit Fuse Chapter](#)

[Bussmann Full Line Catalog](#)

Compliance information

[RoHS Search Tool](#)

Multimedia

[Bussmann series Fuseology](#)

[The Power of Space](#)

Technical data sheets

[Bussmann series UL Class CF CUBEFuse data sheet no. 9000](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TCF30

Catalog Number: TCF30

Eaton Bussmann series TCF fuse, 30 A, 60 Hz, 50 Hz, Dual, Class CF, Black, With indicator, Blade end, Class CF, Time delay, 100 kAIC at 300 Vdc, 300 kAIC at 600 V, Glass filled PES, 600 V, 300 Vdc



General specifications

Product Name	Catalog Number
Eaton Bussmann series TCF fuse	TCF30
UPC	Product Length/Depth
051712615037	1.88 in
Product Height	Product Width
1 in	0.75 in
Product Weight	Compliances
0.08 lb	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	

Electrical rating

Amperage Rating

30 A

Frequency rating - max

60 Hz

Frequency rating - min

50 Hz

Interrupt rating

300 kAIC at 600 Vac

100 kAIC at 300 Vdc

Voltage rating

600 Vac, 300 Vdc

Physical details

Color

Black

Fuse type

Class CF

Time delay

Material

Glass filled PES

Number of elements

Dual

General information

Class

Class CF

Connection

Blade end

Fuse indicator

With Indicator

Special features

Finger safe

Used with

TCFH30N, CCP2-3-30CF

Resources

Catalogs

[Low Voltage Branch Circuit Fuse Chapter](#)

[Bussmann Full Line Catalog](#)

Compliance information

[RoHS Search Tool](#)

Multimedia

[Bussmann series Fuseology](#)

[The Power of Space](#)

Technical data sheets

[Bussmann series UL Class CF CUBEFuse data sheet no. 9000](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia