

# Specifications



## Eaton TCF30

Eaton Bussmann series TCF fuse, Bussmann Series Class CF fuse, TCF, time-delay, dual-element current limiting cube fuse, 30 A, indicating fuse, interrupting rating of 100 kA at 300 Vdc and 300 kA at 600 Vac

### General specifications

PRODUCT NAME	Eaton Bussmann series TCF fuse
CATALOG NUMBER	TCF30
UPC	051712615037
PRODUCT LENGTH/DEPTH	1.88 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	0.75 in
PRODUCT WEIGHT	0.08 lb
COMPLIANCES	<a href="#">RoHS Compliant</a>
CERTIFICATIONS	UL Listed CSA Certified

Electrical rating	
AMPERAGE RATING	30 A
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
INTERRUPT RATING	300 kAIC at 600 Vac 100 kAIC at 300 Vdc
VOLTAGE RATING	600 Vac, 300 Vdc

General information	
CLASS	Class CF
CONNECTION	Blade end
FUSE INDICATOR	With Indicator
SPECIAL FEATURES	Finger safe
USED WITH	TCFH30N, CCP2-3-30CF

Physical details	
COLOR	Black
FUSE TYPE	Class CF Time delay
MATERIAL	Glass filled PES
NUMBER OF ELEMENTS	Dual

Resources	
CATALOGS	<a href="#">Low Voltage Branch Circuit Fuse Chapter</a> <a href="#">Bussmann Full Line Catalog</a>
COMPLIANCE INFORMATION	<a href="#">RoHS Search Tool</a>
MULTIMEDIA	<a href="#">The Power of Space</a> <a href="#">Bussmann series Fuseology</a>
TECHNICAL DATA SHEETS	<a href="#">Bussmann series UL Class CF CUBEFuse data sheet no. 9000</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE: