

TEMPORARY LED HIGH BAY FIXTURE CATALOG NUMBER KT-TFLED100-850 /G2





DESCRIPTION

Easy-to-install, portable, flexible, lightweight temporary lighting; 3-prong USA plug





APPLICATION

Used for indoor applications in place of fluorescent shop lights, surface-mount, and/or strip fixtures.

PRODUCT FEATURES


- Omni-Directional Light Distribution
- Efficacy: 100lm/W
- 6KV Surge Protection
- Strong, Durable Construction
- Suitable for Construction Areas, Outdoor Activity Lighting
- IP64 Rated

- Lightweight
- Isolated Driver for Better Heat Dissipation
- Driver with Heat Sink Silicone is Waterproof, Dust-Proof, and Anti-Mosquito
- Operating Temperature: -40°C/-40°F-60°C/140°F
- Linkable end to end: Total of 5A max in Parallel Connection with self-recovery fuse.

PERFORMANCE SPECIFICATIONS

Catalog Number	Power Consumption	LED Quantity	Power Factor	CRI	Input Voltage	Frequency	Color Temp.	Total Lumens	Metal Halide Equivalent
KT-TFLED100-850 /G2	100W	300	≥0.90	≥80	120V	50~60Hz	5000K	10,000	400W

OPERATING SPECIFICATIONS






Keystone Technologies • 1390 Welsh Road, North Wales, PA 19454 • Phone (800) 464-2680 • Fax (888) 966-0556 • www.keystonetech.com



TEMPORARY LED HIGH BAY FIXTURE CATALOG NUMBER KT-TFLED100-850 /G2

PHYSICAL SPECIFICATIONS



CATALOG NUMBER BREAKDOWN

