



## THHN10BKPCS THHN 1/0 STR Black PCS

*Southwire Company*



Catalog Number	THHN10BKPCS
Manufacturer	Southwire Company
Description	THHN Building Wire, Heat, Moisture, Gasoline and Oil Resistant; Simpull(R) Technology For Easier Pulling; Sunlight Resistant Additional Information, Commercial; Industrial Application, Black, Copper Conductor Material, 1/0 Awg Conductor Size, 125 A (60°C); 150 A (75°C); 170 A (90°C) Current Rating, PVC Insulation Material, 50 Mil Insulation Thickness, Nylon Jacket Material, Made In Usa, +90 °C Maximum Operating Temperature, 19 - Strands, 474 Mil Outside Diameter, Reel; Spool Package Type, Csa C22.2 No. 75; Federal
Weight per unit	0.3710 (lbs/ft)
Product Category	THHN-T90-STR (Stranded)

### Features

Tip Size	By-the-foot
----------	-------------

### Descriptions

Description	THHN 1/0 STR BLACK PCS
-------------	------------------------

### Manufacturer Information

Brand	Copper
-------	--------

### Taxonomies, Classifications, and Categories

Category Description	BUILDING WIRE
----------------------	---------------

### Packaging

Carton	1
Weight Per foot	0.371