



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## THHN20WH2500 THHN 2/0 STR White 2500' *Southwire Company*

Catalog Number	THHN20WH2500
Manufacturer	Southwire Company
Description	THHN Building Wire, Heat, Moisture, Gasoline and Oil Resistant;Simpull(R) Technology For Easier Pulling;Sunlight Resistant Additional Information, Commercial;Industrial Application, White, Copper Conductor Material, 2/0 Awg Conductor Size, 145 A (60°C);175 A (75°C);195 A (90°C) Current Rating, PVC Insulation Material, 50 Mil Insulation Thickness, Nylon Jacket Material, Made In Usa, +90 °C Maximum Operating Temperature, 19 - Strands, 518 Mil Outside Diameter, 2500 FT Overall Length, Reel;Spool Package Type,
Weight per unit	0.4620 (lbs/ft)
Product Category	THHN-T90-STR (Stranded)

### Features

media	Yes
Number of Conductors	1

### Dimensions and Weight

Length	2500
--------	------

### Descriptions

Description	THHN 2/0 STR WHITE 2500'
extra long description	SWC 55611104 THHN 2/0 Str Cu SIM We
Special Features	No Lube

### Manufacturer Information

Brand	Copper
GTIN	00032886913594
Manufacturers Part Number	55611104
UPC	032886913594

### Taxonomies, Classifications, and Categories

Category Description	BUILDING WIRE
Type	THHN-2

### Availability

minimum qty	2500
-------------	------

### Packaging

Carton	2500
Weight Per foot	0.462