



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



THHN5000R2500 THHN 500 STR Orange 2500' Southwire Company

Catalog Number	THHN5000R2500
Manufacturer	Southwire Company
Description	THHN Building Wire, Heat, Moisture, Gasoline and Oil Resistant;Simpull(R) Technology For Easier Pulling;Sunlight Resistant Additional Information, Commercial;Industrial Application, Orange Color, Copper Conductor Material, 500 Kcmil Conductor Size, 320 A (60°C);380 A (75°C);430 A (90°C) Current Rating, PVC Insulation Material, 60 Mil Insulation Thickness, Nylon Jacket Material, Made In Usa, +90 °C Maximum Operating Temperature, 37 - Strands, 926 Mil Outside Diameter, 2500 FT Overall Length, Reel;Spool Pack
Weight per unit	1.7 (lbs/ft)
Product Category	THHN-T90-STR (Stranded)

Features

media	Yes
Number of Conductors	1

Dimensions and Weight

Length	2500
--------	------

Descriptions

Description	THHN 500 STR ORANGE 2500'
extra long description	SWC 55617207 THHN 500 Str Cu SIM Oe
Special Features	No Lube

Manufacturer Information

Brand	Copper
GTIN	00032886872976
Manufacturers Part Number	55617207
UPC	032886872976

Taxonomies, Classifications, and Categories

Category Description	BUILDING WIRE
Type	THHN-2

Availability

minimum qty	2500
-------------	------

Packaging

Carton	2500
Weight Per foot	1.653