



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## THHN80R1000 THHN 8 STR Orange 1000' *Southwire Company*

Catalog Number	THHN80R1000
Manufacturer	Southwire Company
Description	THHN Building Wire, Heat, Moisture, Gasoline and Oil Resistant;Simpull(R) Technology For Easier Pulling Additional Information, Commercial;Industrial Application, Orange Color, Copper Conductor Material, 8 Awg Conductor Size, 40 A (60°C);50 A (75°C);55 A (90°C) Current Rating, PVC Insulation Material, 30 Mil Insulation Thickness, Nylon Jacket Material, Made In Usa, +90 °C Maximum Operating Temperature, 19 - Strands, 213 Mil Outside Diameter, 1000 FT Overall Length, Reel;Spool Package Type, Csa C22.2 No. 75
Weight per unit	0.0630 (lbs/ft)
Product Category	THHN-T90-STR (Stranded)

### Features

media	Yes
Number of Conductors	1

### Dimensions and Weight

Length	1000
--------	------

### Descriptions

Description	THHN 8 STR ORANGE 1000'
extra long description	SWC 23849306 THHN 8 Str Cu SIM Oe 1
Special Features	No Lube

### Manufacturer Information

Brand	Copper
GTIN	00032886231469
Manufacturers Part Number	23849306
UPC	032886231469

### Taxonomies, Classifications, and Categories

Category Description	BUILDING WIRE
Type	THHN-2

### Availability

minimum qty	1000
-------------	------

### Packaging

Carton	1000
Weight Per foot	0.063