



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



THHN80R2500 THHN 8 STR Orange 2500' *Southwire Company*

Catalog Number	THHN80R2500
Manufacturer	Southwire Company
Description	THHN Building Wire, Heat, Moisture, Gasoline and Oil Resistant;Simpull(R) Technology For Easier Pulling Additional Information, Commercial;Industrial Application, Orange Color, Copper Conductor Material, 8 Awg Conductor Size, 40 A (60°C);50 A (75°C);55 A (90°C) Current Rating, PVC Insulation Material, 30 Mil Insulation Thickness, Nylon Jacket Material, Made In Usa, +90 °C Maximum Operating Temperature, 19 - Strands, 213 Mil Outside Diameter, 2500 FT Overall Length, Reel;Spool Package Type, Csa C22.2 No. 75
Weight per unit	0.0630 (lbs/ft)
Product Category	THHN-T90-STR (Stranded)

Features

media	Yes
Number of Conductors	1

Dimensions and Weight

Length	2500
--------	------

Descriptions

Description	THHN 8 STR ORANGE 2500'
extra long description	SWC 23849301 THHN 8 Str Cu SIM Oe 2
Special Features	No Lube

Manufacturer Information

Brand	Copper
GTIN	00032886231476
Manufacturers Part Number	23849301
UPC	032886231476

Taxonomies, Classifications, and Categories

Category Description	BUILDING WIRE
Type	THHN-2

Availability

minimum qty	2500
-------------	------

Packaging

Carton	2500
Weight Per foot	0.063