
TAMPER-RESISTANT FLOOR BOX BRASS COVER

TM1542TRCF | [Pass & Seymour](#)



FEATURES & BENEFITS

High-profile Brass Cover, fits any floor finish - including carpeting, linoleum, tile floors; includes 885 15 amp, 125 volt Decorator Duplex receptacle and will accept any decorator device. Cover includes captive screws to prevent loss.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Tamper-Resistant shutters let plugs in, keep other things out.
- Durable construction, impact, and scratch resistant PVC construction.
- Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.
- Auto/Clamps and knockouts on both sides of box.
- Meets UL514(c) scrub water exclusion test.
- Threaded device mounting holes.
- Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.
- Ready for low-voltage wiring, drill guides on underside of cover.
- UL and cUL Listed. Captive screws on TM1542 Series -- screws will not be lost -- new.
- Made in USA.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater

Component Type: Covers & Flanges

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121308

UR: No

DIMENSIONS

Diameter (US): 6.5"

TECHNICAL INFORMATION

Material: Brass

Floor Type: Wood

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

