



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TM874DBCC6 4W Deco SW 15A 120/277V DRK Brnze *Pass & Seymour/Legrand*

Catalog Number	TM874DBCC6
Manufacturer	Pass & Seymour/Legrand
Description	15A 120/277V Switch Decorator 4-Way, Dark Bronze
Weight per unit	0.2820 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Rating	120V
Material	Thermoplastic
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
operating cycles	50000
Poles	4-Way, Single Pole
Switch Type	Paddle
Voltage	120/277 V
Voltage Rating	120

Material, Color, and Finish

Color	Dark Bronze
-------	-------------

Dimensions and Weight

Size	1.27" Depth x 1.43" Width x 4.19" Height
------	--

Descriptions

Description	4W DECO SW 15A 120/277V DRK BRNZE
extra long description	P&S TM874DBCC6 4W DECO SW 15A 120/2
Long Description	15A 120/277V Switch Decorator 4-Way, Dark Bronze
Product Type	4W Deco SW 15A 120/277V DRK Brnze
Special Features	Everyone wants a home that's a step above ordinary. Now the radiant® collection of switches, outlets, dimmers and home automation controls by Legrand puts that stylish finishing touch affordably within reach. radiant gets rid of unsightly screws, delivering clean looks in a range of colors and metallic finishes.

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007029468
Manufacturers Part Number	TM874-DBCC6
UPC	785007029468



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Decorator Switch

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Weight Per each	0.282

Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximun continuous +115°C, minimum -40°C
standard	CULUS, CSA Listed, UL Listed