



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMC6206 2" Cord Grips

Crouse-Hinds

Catalog Number	TMC6206
Manufacturer	Crouse-Hinds
Description	TMC Armored Cable Gland, Aluminum, 2 In Size, 4.5 In (Gland) Length, -25 °C Operating Temperature, +60 °C Operating Temperature, Grip Connection, Non-Insulated, 2.35 LB/Ea
Weight per unit	2.4 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

connection	Male NPT
dimensions	5.5000 IN X 3.5000 IN X 3.5000 IN

Descriptions

Description	2" CORD GRIPS
extra long description	CRS-H TMC6206 2 AL FT MCCAB ARMOR O
Features	For use with metal-clad cable, TECK corrugated cable or interlocked steel or aluminum cable, Crouse-Hinds series TMC cable glands provide a means for terminating at junction boxes, control centers, panelboards and enclosures for motor control and electrical distribution equipment. TMC cable glands form a mechanical watertight connection and may installed in Class I, Division 2 locations provided there are no arcing and sparking risks in accordance with NEC501.10B.

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274414591
UPC	782274414591

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland

Packaging

Carton	1
Weight Per each	2.401

Uses, Certifications, and Standards

Enclosure	IP56
standard	UL (CANADA AND US), CUL
Temperature Rating	-25 To 60 Deg C