

Eaton TMC8302

Catalog Number: TMC8302

Eaton Crouse-Hinds series TMC cable gland, Metal-clad, TECK corrugated or interlocked steel, or aluminum, Armoured, Aluminum, Outer sheath: 2.52-3.28", General purpose, 3" NPT, Armor range: 2.45-3.02"



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series TMC cable gland	TMC8302
	UPC
	782274414621
Product Length/Depth	Product Height
6.32 in	4.88 in
Product Width	Product Weight
4.88 in	4.4 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Protection type

General purpose

Cable type

Metal-clad, TECK corrugated or interlocked steel, or aluminum

Gland type

Armoured

Material

Aluminum

Thread Size

3"

Thread type

NPT

Armor (min/max)

2.45-3.02"

Outer sheath (min/max)

2.52-3.28"

Resources

Catalogs

[Crouse-Hinds series TMC catalog page](#)

Certification reports

[TMC Armoured Gland UL certification](#)

Installation instructions

[IF 1183 - Terminator Cable Fittings](#)

Specifications and datasheets

[Eaton Specification Sheet - TMC8302](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)