

Eaton TMCX10402

Catalog Number: TMCX10402

Eaton Crouse-Hinds series TMCX cable gland, Metal-clad corrugated, TECK armoured and tray cable, Armoured barrier and non-armoured barrier, Aluminum, Outer Sheath: 3.58-4.28", 4" NPT, Armor Range: 3.50-4.02"

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series TMCX cable gland	TMCX10402
	UPC
	782274414768
Product Length/Depth	Product Height
9.94 in	5.88 in
Product Width	Product Weight
5.88 in	11.95 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

NEMA Rating

4

Product specifications

Protection type

Explosion-proof

Cable type

Metal-clad with interlocked or continuously welded corrugated armoured

TECK armoured

Tray cable

Gland type

Armoured Barrier and Non-armoured Barrier

Material

Aluminum

Thread Size

4"

Thread type

NPT

Armor (min/max)

3.50-4.02"

Outer sheath (min/max)

3.58-4.28"

Resources

Catalogs

[Crouse-Hinds series TMCX catalog page](#)

Certification reports

[TMCX Explosionproof Armoured Barrier Gland UL certification](#)

Installation instructions

[IF 1184 - TMCX Terminator Cable Fittings](#)

Specifications and datasheets

[Eaton Specification Sheet - TMCX10402](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)