

Eaton TMCX3112

Catalog Number: TMCX3112

Eaton Crouse-Hinds series TMCX cable gland, Metal-clad corrugated, TECK armoured and tray cable, Armoured barrier and non-armoured barrier, Aluminum, Outer Sheath: 0.85-1.31", 1" NPT, Armor Range: 0.80-1.12"



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series TMCX cable gland	TMCX3112
	UPC
	782274414683
Product Length/Depth	Product Height
4.07 in	2 in
Product Width	Product Weight
2 in	0.68 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

NEMA Rating

4

Product specifications

Protection type

Explosion-proof

Cable type

Tray cable

TECK armoured

Metal-clad with interlocked or continuously welded corrugated armoured

Gland type

Armoured Barrier and Non-armoured Barrier

Material

Aluminum

Thread Size

1"

Thread type

NPT

Armor (min/max)

0.80-1.12"

Outer sheath (min/max)

0.85-1.31"

Resources

Catalogs

[Crouse-Hinds series TMCX catalog page](#)

Certification reports

[TMCX Explosionproof Armoured Barrier Gland UL certification](#)

Installation instructions

[IF 1184 - TMCX Terminator Cable Fittings](#)

Specifications and datasheets

[Eaton Specification Sheet - TMCX3112](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)