

Eaton TMCX4140

Catalog Number: TMCX4140

Eaton Crouse-Hinds series TMCX cable gland, Metal-clad corrugated, TECK armoured and tray cable, Armoured barrier and non-armoured barrier, Aluminum, Outer Sheath: 1.15-1.62", 1-1/4" NPT, Armor Range: 1.10-1.40"



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series TMCX cable gland	TMCX4140
	UPC
	782274414690
Product Length/Depth	Product Height
4.1 in	2.44 in
Product Width	Product Weight
2.44 in	1.08 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

NEMA Rating

4

Product specifications

Protection type

Explosion-proof

Cable type

TECK armoured

Tray cable

Metal-clad with interlocked or continuously welded corrugated armoured

Gland type

Armoured Barrier and Non-armoured Barrier

Material

Aluminum

Thread Size

1-1/4"

Thread type

NPT

Armor (min/max)

1.10-1.40"

Outer sheath (min/max)

1.15-1.62"

Resources

Catalogs

[Crouse-Hinds series TMCX catalog page](#)

Certification reports

[TMCX Explosionproof Armoured Barrier Gland UL certification](#)

Installation instructions

[IF 1184 - TMCX Terminator Cable Fittings](#)

Specifications and datasheets

[Eaton Specification Sheet - TMCX4140](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)