

# Eaton TN224ZN

Catalog Number: TN224ZN

Eaton B-Line series Twirl-Nut nut, 0.25"Hx1.375"Lx0.85"W, Steel, Electro-plated, 3/8"-16 bolt size, 300 lbs load, 300 lbs load

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series Twirl-Nut nut	TN224ZN
UPC	Product Length/Depth
781011401436	1.375 in
Product Height	Product Width
0.25 in	0.85 in
Product Weight	Certifications
0.067 lb	Not Applicable

## Model

### Bolt/thread/rod size

3/8"-16

### Product Category

Channel nuts

### Type

Twirl-nut

## Load rating/capacity

### Load rating (pull out strength)

300 lbs

### Load rating (slip strength)

300 lbs

## Material/finish

### Finish

Electro-plated

### Material

Steel

## Resources

### Catalogs

[B-Line Series Strut Systems Catalog](#)

[B-Line Safety Gratings Full Catalog](#)

[Channel Nuts and Hardware Catalog Section](#)

### Specifications and datasheets

[Eaton Specification Sheet - TN224ZN](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)