



BURNDY Catalog Number
UPC Number

TP1610F
7818107148811

Description

FORK- 22- 16 AWG- VINYL, 0.95
IN L

Status

Active

Web Use

BURNDY Product Line

Dimensional

Max Insulation Diameter 0.145
Length (in) 0.95
Tongue Type Fork
Pad Width (in) 0.41
Strip Length 13/64

Electrical

Max Voltage Rating 600

General

Product Description

Fork Tongue Copper Terminal, 22-
16 Max. Insul. Dia. Accom.: .145
Color Code: Red, 8-10, .95 in L,
.41 in W, Polyvinylchloride
Insulation

Other

Bulk Package BA16EF10M

Physical

Type of Plating Tin
Connector Type Terminal - Fork
Color Code Red
Insulation Type Vinyl
Plated (Yes or No) Y

Approvals / Certifications

UL Listed Y
CSA Certified Y
ROHS Compatible Compliant
UL Recognized N
CULUS N

Conductor(s)

Copper Solid Size (Range) N/A
Copper Stranded (Range) 20 AWG-16 AWG

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175