

Specifications



Eaton TP292

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 2-1/8", Steel, (2) 1/2", (2) 3/4", Fixture rated, 21.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series octagon outlet box
CATALOG NUMBER	TP292
UPC	786189102925
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.64 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
DEPTH	2-1/8"
CAPACITY	21.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)

SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated

Resources

CATALOGS	Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page
CERTIFICATION REPORTS	Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP292 Steel Outlet Boxes for Electrical Systems

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP292

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 2-1/8", Steel, (2) 1/2", (2) 3/4", Fixture rated, 21.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series octagon outlet box
CATALOG NUMBER	TP292
UPC	786189102925
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.64 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
DEPTH	2-1/8"
CAPACITY	21.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)

SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated

Resources

CATALOGS	Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page
CERTIFICATION REPORTS	Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP292 Steel Outlet Boxes for Electrical Systems

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

