

Specifications



Eaton TP632

Eaton Crouse-Hinds series Gang Box, (6) 1/2" and 3/4" concentric, VP, Conduit (no clamps), 2-1/2", (2) 1/2" and 3/4" concentric, Steel, Three-gang, (3) 1/2" and 3/4" concentric, Non-gangable, 46.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series gang box
CATALOG NUMBER	TP632
UPC	786189106329
PRODUCT LENGTH/DEPTH	5.56 in
PRODUCT HEIGHT	2.5 in
PRODUCT WIDTH	3.75 in
PRODUCT WEIGHT	1.43 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	2-1/2"
TYPE	Non-gangable
NUMBER OF GANGS	Three-gang
CAPACITY	46.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)
BRACKET STYLE	VP
END KNOCKOUTS	(2) 1/2 in and 3/4 in concentric
SIDE KNOCKOUTS	(3) 1/2 in and 3/4 in concentric
BOTTOM KNOCKOUTS	(6) 1/2 in and 3/4 in concentric
MATERIAL	Steel

Resources

CATALOGS	Crouse-Hinds series Steel Switch Boxes catalog page
CERTIFICATION REPORTS	Steel Switch Boxes Canadian certification Steel Switch Boxes UL certification
SPECIFICATIONS AND DATASHEETS	Steel Outlet Boxes for Electrical Systems Eaton Specification Sheet - TP632

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

