

Eaton TP683

Catalog Number: TP683

Eaton Crouse-Hinds series Masonry Box, (4) 1/2", (4) 3/4", 2-1/2", (2) 1/2", (2) 3/4", Steel, Two-gang, (2) 1/2", (2) 3/4", 31.0 cubic inch capacity




Photo is representative

General specifications

| | |
|---------------------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series masonry box | TP683 |
| UPC | Product Length/Depth |
| 786189106831 | 3.75 in |
| Product Height | Product Width |
| 3.75 in | 3.75 in |
| Product Weight | |
| 1.03 lb | |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Depth

2-1/2"

Number of gangs

Two-gang

End Knockouts

(2) 1/2 in, (2) 3/4 in

Side knockouts

(2) 1/2 in, (2) 3/4 in

Bottom Knockouts

(4) 1/2 in, (4) 3/4 in

Capacity

31 cubic in

Material

Steel

Resources

Catalogs

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

Certification reports

[Steel Masonry Boxes Canadian certification](#)

[Steel Masonry Boxes UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP683](#)

[Steel Outlet Boxes for Electrical Systems](#)