



TAMPER-RESISTANT COMMERCIAL GRADE RECEPTACLES, WHITE, TR15W

TR15W | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Commercial Grade Receptacle, 15A, 125V, White

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- High Impact resistant nylon face.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive steel terminal screws. Side wire only.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White
Type: Receptacles
Features: Tamper-Resistant
Number Of Poles: 2
Number Of Wires: 3
Special Features: Side Wire Only, Tamper-Resistant
Style: Duplex

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): .65"
Height (US): 3.28"

Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15R

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Commercial

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





TAMPER-RESISTANT COMMERCIAL GRADE RECEPTACLES, WHITE, TR15W

TR15W | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Commercial Grade Receptacle, 15A, 125V, White

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- High Impact resistant nylon face.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive steel terminal screws. Side wire only.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White
Type: Receptacles
Features: Tamper-Resistant
Number Of Poles: 2
Number Of Wires: 3
Special Features: Side Wire Only, Tamper-Resistant
Style: Duplex

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): .65"
Height (US): 3.28"

Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15R

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Commercial

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

