



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TR15W Duplex Recept TR 15A/125V WH

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | TR15W   |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | Tamper-Resistant Commercial Grade Receptacle, 15A, 125V. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page. |
| Weight per unit  | 0.2478 (lbs/each)   |
| Product Category | Gen Purpose Recept & Surge Pro  |

### Features

|                     |  |
|---------------------|--|
| amperage rating     | 15   |
| connection          | Side wire  |
| Dielectric Strength | Withstands 1500V minimum                         |
| indoor/outdoor      | Indoor   |
| Material            | Nylon  |
| media               | Yes  |
| Number of Wires     | 3  |
| Outlet Type         | Commercial, Indoor, Tamper-Resistant             |
| Poles               | Double Pole                                      |
| Voltage             | 125.0 V  |
| Voltage Rating      | 125  |
| Wattage             | Electrical power is expressed in Amps and Volts. |
| Wire Size           | 14 - 10  |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | White |
| Finish | Matte |

### Dimensions and Weight

|        |       |
|--------|-------|
| Height | 3.281 |
| Width  | 1.130 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | DUPLEX RECP TR 15A/125V WH  |
| extra long description | P&S TR15W RECEP DUP TAMPER RESIS 15   |
| Long Description       | Tamper-Resistant Commercial Grade Receptacle, 15A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.   |
| Product Type           | Recep Dup Tamper Resis 15A/125V WH  |
| Special Features       | Dual mechanical shutter system to help prevent insertion of foreign objects. Auto-ground clip assures positive ground. Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. Backed-out tri-drive steel terminal screws for faster installation. Side wire capability. Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly. .032 inch thick brass triple-wipe power contacts. Two drive screws anchor steel st |

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007241594         |
| Manufacturers Part Number | TR15-W                 |
| UPC                       | 785007241594           |

## Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type                 | Outlet               |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 100    |
| Weight Per each | 0.2478 |

## Uses, Certifications, and Standards

|                          |                                      |
|--------------------------|--------------------------------------|
| Application              | Commercial                           |
| environmental conditions | Flammability: UL94 V2                |
| Mounting                 | WALL                                 |
| nema rating              | 5-15R                                |
| standard                 | CULUS, cULus UL498, CSA C22.2 No. 42 |
| Temperature Rating       | -40° - 50° C                         |