

# Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, White

TR26362W



Tamper-Resistant Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt White



## features & benefits

- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive brass terminal screws for faster installation.
- Internal screw-pressure-plate back and side wire capability.
- Two back wire holes for additional wiring flexibility.
- Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
- .032 inch thick brass triple-wipe power contacts.
- Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

## specifications

### General Info

Color: white  
Type: Receptacles  
Duty: Heavy Duty  
Special Features: tamper-resistant,back,side wire  
Style: Decorator

### **Listing Agencies/Third Party Information**

CSA Standard: Yes  
cUL Standard: Yes  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406

### **Dimensions**

Depth U S: 0.833"  
Height U S: 3.281"  
Width U S: 1.322"

### **Technical Information**

Amps: 20 Amp  
Volts: 125V  
Volts A C: 125  
Capacity: Duplex  
Grade Type: Federal Specification

### **Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant