

Specifications



Eaton TR270W

Eaton residential grade duplex receptacle, #14-10 AWG, 15A, Commercial, Residential, Flush, 125V, Side and push, White, Brass, Impact-resistant thermoplastic face, PVC body, 5-15R, Duplex, Screw, Thermoplastic, Core pack

General specifications

PRODUCT NAME	Eaton residential grade duplex receptacle
CATALOG NUMBER	TR270W
UPC	032664666537
PRODUCT LENGTH/DEPTH	1.24 in
PRODUCT HEIGHT	4 in
PRODUCT WIDTH	0.79 in
PRODUCT WEIGHT	0.125 lb
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Residential grade

Product specifications

DEVICE TYPE	Receptacle
TYPE	Duplex receptacle
AMPERAGE RATING	15A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Tamper resistant
APPLICATION	Commercial/residential
DEVICE GRADE	Standard grade
WIRING METHOD	Side and push
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Standard
MATERIAL	Thermoplastic
PACKAGING TYPE	Core pack
COLOR	White
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Push-In Terminals Wiring: #14 AWG copper (CU) Only, Side Wiring: #10-14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-15R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	PVC body Impact-resistant thermoplastic face
RECEPTACLE TYPE	Duplex

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

MULTIMEDIA	Residential straight blade receptacles
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TR270W Duplex tamper resistant receptacles spec sheet



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

