



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5251 SGL Recp TR 15A/125V BN

Pass & Seymour/Legrand

Catalog Number	TR5251
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Construction Spec Grade Single Receptacles, Back and Side Wire, 15A, 125V
Weight per unit	0.1780 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Number of Wires	3
Outlet Type	Indoor, Commercial, Tamper-Resistant
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Color	Brown
-------	-------

Dimensions and Weight

Height	3.28
Width	1.190

Descriptions

Description	SGL RECP TR 15A/125V BN
extra long description	P&S TR5251 RECEPT SGL TAMPER RESIS 1
Long Description	Tamper-Resistant Construction Spec Grade Single Receptacles, Back and Side Wire, 15A, 125V
Product Type	Recep SGL Tamper Resis 15A/125V BN
Special Features	Dual mechanical shutter system to help prevent insertion of foreign objects. Two drive screws anchor strap to back body and face where abrupt removal torque is greatest. Heavy-duty corrosion-resistant zinc-plated steel strap for added strength. Backed-out tri-drive steel terminal screws for faster installation. Internal screw-pressure-plate back and side wire capability. Two back wire holes for additional wiring flexibility. One-piece brass triple-wipe power contacts for lasting retention.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007241990
Manufacturers Part Number	TR5251
UPC	785007241990

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.178

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-15R
standard	CULUS, UL498, CSA C22.2 No. 42
Temperature Rating	-40° - 60° C