

Tamper-Resistant Construction Spec Grade Single Receptacles, Back & Side Wire, 15A, 125V, White

TR5251W



Tamper-Resistant Construction Spec Grade Single Receptacle Back & Side Wire 15amp 125volt White



features & benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.

specifications

General Info

Color: white
Type: Single, Receptacles
Number Of Poles: 2
Number Of Wires: 3
Special Features: Tamper-Resistant,back,side wire

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406
UR: No

Dimensions

Depth U S: 1.19"
Height U S: 3.28"
Width U S: 1.296"

Technical Information

Amps: 15 Amp
NEMA Configuration Number: 5-15R
Volts: 125V
Volts A C: 125
Capacity: Single
Grade Type: Construction

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant