



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5351LA Recep SGL Tamper Resis 20A/125V La

Pass & Seymour/Legrand

Catalog Number	TR5351LA
Manufacturer	Pass & Seymour/Legrand
Description	Single Receptacle, 20 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Back and Side Wired Connection, Wall Mount, 1.296 In Length, 1.190 In Width, 3.28 In Height, Nylon Material, Light Almond, Heavy Duty Corrosion Resistant, 0.1700 LB
Weight per unit	0.1732 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
media	Yes
Outlet Type	Indoor, Commercial, Tamper-Resistant
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Descriptions

Description	RECEP SGL TAMPER RESIS 20A/125V LA
extra long description	P&S TR5351LA RECEP SGL TAMPER RESIS

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007241952
Manufacturers Part Number	TR5351LA
UPC	785007241952

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	10
Package	100
Weight Per each	0.1732



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
standard	CULUS, UL498, CSA C22.2 No. 42
Temperature Rating	-40° - 60° C