



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5362RED Duplex Recept TR B+S Wire 20A/125V RD

Pass & Seymour/LeGrand

Catalog Number	TR5362RED
Manufacturer	Pass & Seymour/LeGrand
Description	Tamper-Resistant Hard Use Spec Grade Receptacle, Back and Side Wire, 20A, 125V
Weight per unit	0.2182 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Number of Wires	3
Outlet Type	Tamper-Resistant
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Color	Red
Finish	Matte

Dimensions and Weight

Height	3.281
Width	1.130



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	DUPLEX RECP TR B+S WIRE 20A/125V RD
extra long description	P&S TR5362RED RECEP DUP TR B+S WIRE
Long Description	Tamper-Resistant Hard Use Spec Grade Receptacle, Back and Side Wire, 20A, 125V
Product Type	Recep Dup TR B+S Wire 20A/125V Red
Special Features	Dual mechanical shutter system to help prevent insertion of foreign objects. Auto-ground clip assures positive ground. Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. Backed-out tri-drive brass terminal screws for faster installation. Internal screw-pressure-plate back and side wire capability. Two back wire holes for additional wiring flexibility. Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/bod

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007243734
Manufacturers Part Number	TR5362-RED
UPC	785007243734

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.2182

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	CULUS, UL498, CSA C22.2 No. 42
Temperature Rating	-40° - 60° C