



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5362USBGRY Dup Rec 20A TR Spec W/3.1A Usb CHRG Gy *Pass & Seymour/Legrand*

Catalog Number	TR5362USBGRY
Manufacturer	Pass & Seymour/Legrand
Description	Combination 20A 125V Tamper-Resistant Duplex Outlet With Two Usb Chargers - Gray
Weight per unit	0.3392 (lbs/each)
Product Category	Combination Devices

Features

amperage rating	20
connection	Side & Back Wired
Dielectric Strength	Withstands 2000V minimum
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	125
Wire Size	14 -10

Dimensions and Weight

Depth	1.392
Height	3.281
Width	1.693

Descriptions

Description	DUP REC 20A TR SPEC W/3.1A USB CHRG GY
extra long description	P&S TR5362USBGRY DUP REC 20A TR SPE
Long Description	Combination 20A 125V Tamper-Resistant Duplex Outlet with Two USB Chargers - Gray
Product Type	Dup Rec 20A TR Spec W/3.1A Usb CHRG Gy
Special Features	Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007031850
Manufacturers Part Number	TR5362USBGRY
UPC	785007031850

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	Tamper-Resistant USB Duplex Receptacle



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	50
Weight Per each	0.3392

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	UL94 V2
Mounting	BOX
nema rating	5-20R
standard	CSA Listed, cULus, FSUL, UL Listed, RoHS