



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5362USBW Duplex Recp 20A TR Spec W/3.1A Usb Charge WH

Pass & Seymour/Legrand

Catalog Number	TR5362USBW
Manufacturer	Pass & Seymour/Legrand
Description	Duplex Receptacle, 2 Poles, 20 A, 125 V, #14 to #10 Awg Wire Size, White, 3 Wires, Thermoplastic, 1.392 (D) X 1.693 (W) X 3.281 (H) In, Box Mount, -40 °C Operating Temperature, +60 °C Operating Temperature, 0.34 LB
Weight per unit	0.3392 (lbs/each)
Product Category	Combination Devices

Features

amperage rating	20
connection	Side & Back Wired
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Outlet Type	Tamper-Resistant, USB-Charging
Phase	1
Poles	2
Voltage	125.0 V
Voltage Rating	125

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Depth	1.392
Height	3.281
Width	1.693

Descriptions

Description	DUPLEX RECP 20A TR SPEC W/3.1A USB CHARGE WH
extra long description	P&S TR5362USBW DUP REC 20A TR SPEC

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007031669
UPC	785007031669

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	Outlet

Trade Size

Amperage	20.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	50
Weight Per each	0.3392

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	UL94 V2
Mounting	BOX
standard	CULUS, UL, CSA Listed, cULus, FSUL, UL Listed, RoHS, FEDSPEC