



## TAMPER-RESISTANT HOSPITAL GRADE RECEPTACLES, BACK & SIDE WIRE, 20A, 125V, IVORY

TR63HI | [Pass & Seymour](#)

### FEATURES & BENEFITS

Tamper-Resistant Hospital Grade Duplex Receptacle Back & Side Wire 20amp 125volt Ivory

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground.
- One-piece, nickel-plated brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory

Type: Receptacles

Special Features: Tamper-Resistant,back, side wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

UR: No

## DIMENSIONS

Depth (US): 0.9"

Height (US): 3.281"

Width (US): 1.625"

## TECHNICAL INFORMATION

Amps: 20A

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Hospital

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





## TAMPER-RESISTANT HOSPITAL GRADE RECEPTACLES, BACK & SIDE WIRE, 20A, 125V, IVORY

TR63HI | [Pass & Seymour](#)

### FEATURES & BENEFITS

Tamper-Resistant Hospital Grade Duplex Receptacle Back & Side Wire 20amp 125volt Ivory

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground.
- One-piece, nickel-plated brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory

Type: Receptacles

Special Features: Tamper-Resistant,back, side wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

UR: No

## DIMENSIONS

Depth (US): 0.9"

Height (US): 3.281"

Width (US): 1.625"

## TECHNICAL INFORMATION

Amps: 20A

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Hospital

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

