

Specifications



Photo is representative



Eaton TR780W-BOX

Eaton commercial specification grade decorator duplex receptacle, #14-10 AWG, 15A, Commercial, Flush, 125V, Push and side, White, Brass, Impact-resistant thermoplastic face and back body, 5-15R, Duplex, Screw, Thermoplastic, ED Box

General specifications

PRODUCT NAME	Eaton commercial specification grade decorator duplex receptacle
CATALOG NUMBER	TR780W-BOX
UPC	032664750120
PRODUCT LENGTH/DEPTH	2.72 in
PRODUCT HEIGHT	4.48 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.211 lb
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Commercial specification grade



Powering Business Worldwide

Product specifications

DEVICE TYPE	Receptacle
TYPE	Duplex receptacle
AMPERAGE RATING	15A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Recessed Tamper resistant
APPLICATION	Commercial
DEVICE GRADE	Specialty standard
WIRING METHOD	Side and push
NUMBER OF WIRES	3
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Recessed
MATERIAL	Thermoplastic
PACKAGING TYPE	ED Box
COLOR	White
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	Push-In Terminals Wiring: #14 AWG copper (CU) Only, Side Wiring: #10-14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-15R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	Impact-resistant thermoplastic face and back body
RECEPTACLE TYPE	Duplex

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

MULTIMEDIA	Residential straight blade receptacles
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TR780W-BOX Recessed and floor box receptacles spec sheet



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

