


Specifications



Photo is representative



Eaton TRUSBAC15B-BOX

Eaton Combination USB Type A and C Charger, 15 A 5-15 R Receptacle, Brown, USB, Brass, Thermoplastic, Flush, Two-pole, Three-wire, Tamper resistant, Decorator, 125 V

General specifications

PRODUCT NAME	Eaton combination USB charger with duplex receptacle
CATALOG NUMBER	TRUSBAC15B-BOX
UPC	032664755859
PRODUCT LENGTH/DEPTH	1.4 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	1.3 in
PRODUCT WEIGHT	0.285 lb
WARRANTY	1 year
CERTIFICATIONS	NOM cULus Listed
PRODUCT TYPE	Combination USB charger with duplex receptacle

Product specifications

TYPE	Type AC
AMPERAGE RATING	15A
VOLTAGE RATING	125 V
CONTACT MATERIAL	Brass
FEATURES	Tamper resistant 5A Charging
WIRING METHOD	Screw terminals
NUMBER OF WIRES	Three-wire
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
PACKAGING TYPE	Retail Box
COLOR	White Brown
MATERIAL	Thermoplastic
STYLE	Decorator
ALLOWABLE WIRE SIZE	Side or Back Wiring :#10- 14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-15R
TORQUE RATING	14 lbf-inch
COMBINATION TYPE	USB
DESIGN TYPE	Receptacle
RECEPTACLE TYPE	Two-pole, three-wire, grounding

Resources

BROCHURES	5A Slim USB Charging Receptacles
MULTIMEDIA	Introduction to USB-C Duplex Receptacles
	Eaton's USB charging receptacles - Never miss a moment
	Fast and convenient charging made easy with Eaton's USB receptacles
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TRUSBAC15B-BOX
	USB A/C charger tamper resistant receptacle spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

