



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2569 E. Hwy 97
78064-0000, TX Pleasanton
Phone: 830-569-3390
Fax: 830-569-3608



TRVGF20VSP 20A TR GFI IV Dec Duplex Rec *Eaton Wiring Devices*

| | |
|------------------|---------------------------------|
| Catalog Number | TRVGF20VSP |
| Manufacturer | Eaton Wiring Devices |
| Description | Gfci TR Deco Duplex 20A 125V Iv |
| Weight per unit | 3.0 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|---------------------------------------|
| amperage rating | 20 A |
| connection | 4714 Lm |
| Material | Nylon Top Housing, PVC Bottom Housing |
| Poles | 2 Pole/ 3 Wire |
| Voltage Rating | 125 A |

Dimensions and Weight

| | |
|-------|--------|
| Width | 1.3 in |
|-------|--------|

Descriptions

| | |
|------------------|---|
| Description | 20A TR GFI IV DEC DUPLX REC |
| Long Description | GFCI TR Deco Duplex 20A 125V IV |
| Product Type | Gfci TR Deco Duplex 20A 125V Iv |
| Special Features | Specification Grade, Tamper Resistant, Wiring Type Back and Side Wire |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | COOPER WIRING DEVICES |
| GTIN | 00032664668814 |
| Manufacturers Part Number | TRVGF20V-SP |
| sub brand | Arrow Hart |
| UPC | 032664668814 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------|
| Category Description | Commercial receptacles |
| Type | Duplex, GFCI, Straight Blade |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 3 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2569 E. Hwy 97
78064-0000, TX Pleasanton
Phone: 830-569-3390
Fax: 830-569-3608

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | Specific Grade |
| Enclosure | Tamper Resistant NEC Requirements |
| standard | UL mA |