

## Specification Sheet

Part Number: TSR1W-6A

Tamper resistant covers with hidden latch provide security while allowing quick entry for cable maintenance.

PVC construction is lightweight, durable and more affordable than metallic raceway systems.

Flexible hinge is designed to reduce stress cracking and discoloration from repeated opening and closing.

Foam tape backing with rubber based adhesive conforms to any flat surface to assist with temporary positioning and mounting.

Systems and fittings are available in white, office white and ivory to coordinate with a variety of décor.

Fittings incorporate a minimum 1" bend radius to meet TIA/EIA 568-B and 569-A standards.



One Piece Surface Raceway, 3/4", 6.0 ft Long, PVC, White, 120ft/Carton

|                |           |
|----------------|-----------|
| Article Number | 250-01604 |
|----------------|-----------|

|      |         |
|------|---------|
| Type | TSR1-6A |
|------|---------|

|       |            |
|-------|------------|
| Color | White (WH) |
|-------|------------|

|              |        |
|--------------|--------|
| Quantity Per | carton |
|--------------|--------|

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | HellermannTyton surface raceway systems are the ideal solution for routing communication and power cables. No need to break into existing walls - raceway systems are designed to route cable along wall surfaces. Made of a PVC material, components are durable and affordable; and the one-piece construction and adhesive tape backing make positioning and mounting easy. HellermannTyton offers a low voltage TSR system and a power rated TSRP system that are available in three different diameters to accommodate different cable and wire bundle and conduit sizes. Both systems include a complete line of fittings and junction boxes that allow for clean and professional installations. |
| Short Description   | One Piece Surface Raceway, 3/4", 6.0 ft Long, PVC, White, 120ft/Cartron                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Global Part Name    | TSR1-6A-PVC-WH                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Length L (Imperial) | 6.0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Length L (Metric)   | 1.83                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Width W (Imperial)  | 0.75                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Width W (Metric)    | 19.05                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Height H (Imperial) | .50                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Height H (Metric)   | 12.70                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Material            | Polyvinylchloride (PVC)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Material Shortcut   | PVC                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |

|                              |                     |
|------------------------------|---------------------|
| Flammability                 | UL 94 V-0           |
| Halogen Free                 | No                  |
| UV Resistant (Yes/No)        | No                  |
| Use Conditions               | For Indoor Use Only |
| Operating Temperature        | +122°F (+50°C)      |
| Reach Compliant (Article 33) | No                  |
| ROHS Compliant               | Yes                 |
| Package Quantity (Imperial)  | 120.0               |
| Package Quantity (Metric)    | 36.58               |
| Customs Number               | 3925900000          |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)